


## Regal® Flushometer

NOTE: Also for use with Regal® XL  
(Since mid-2010)



The repair kits and parts listed on this page are designed to service all Sloan diaphragm type flushometers, including those manufactured for low consumption (LC) usage.

**ABBREVIATIONS:**  
CP = Chrome plated  
gpf = gallons per flush  
Lpf = Liters per flush  
LC = Low consumption  
pkg = package



## PARTS LIST

| Item No.                                             | Code No.                                        | Part No. | Description                                                                      |
|------------------------------------------------------|-------------------------------------------------|----------|----------------------------------------------------------------------------------|
| 1.                                                   | <b>0317004</b>                                  | R-10     | CP Cover                                                                         |
|                                                      | —                                               | R-10-HE  | CP High Efficiency Cover                                                         |
| 2.                                                   | <b>0301168</b>                                  | A-71     | Inside Cover                                                                     |
| <b>SEE ITEMS 3A THROUGH 6E IN CHART ON NEXT PAGE</b> |                                                 |          |                                                                                  |
| 3A.                                                  | <b>5301058</b>                                  | A-19-AC  | Relief Valve, White (Closet) — 12 per package                                    |
| 3B.                                                  | <b>5301059</b>                                  | A-19-AU  | Relief Valve, Black (Urinal) — 12 per package                                    |
| 3C.                                                  | <b>5301211</b>                                  | A-19-ALC | Relief Valve, Green (Closet/Urinal-LC) — 12 per package                          |
| 3D.                                                  | <b>0301143</b>                                  | A-19-AL  | Relief Valve, Blue (9 Liter Closet)                                              |
| 4.                                                   | <b>5301111</b>                                  | A-15-A   | Disc — for all Inside Parts Kits — 12 per package                                |
| 5.                                                   | <b>5301188</b>                                  | A-156-A  | Diaphragm — for all Inside Parts Kits — 12 per package                           |
| 6A.                                                  | <b>5301236</b>                                  | A-163-A  | Guide Assembly 4.5 gpf/17.0 Lpf Closet & 1.5 gpf/5.7 Lpf Urinal — 12 per package |
| 6B.                                                  | <b>5301032</b>                                  | A-152-A  | Guide Assembly 3.5 gpf/13.2 Lpf Closet — 12 per package                          |
| 6C.                                                  | <b>5301031</b>                                  | A-151-A  | Guide Assembly 1.6 gpf/6.0 Lpf LC Closet — 12 per package                        |
| 6D.                                                  | <b>5301155</b>                                  | A-155-A  | Guide Assembly 1.0 gpf/3.8 Lpf LC Urinal — 12 per package                        |
| 6E.                                                  | <b>5301157</b>                                  | A-157-A  | Guide Assembly 0.5 gpf/1.9 Lpf Urinal — 12 per package                           |
| 7.                                                   | <b>SEE INSIDE PARTS KITS CHART ON NEXT PAGE</b> |          |                                                                                  |
| 8.                                                   | <b>5302297</b>                                  | B-39     | Seal — 12 per package                                                            |
| 9.                                                   | <b>5302279</b>                                  | B-32-A   | CP Handle Assembly — 6 per package                                               |
|                                                      | <b>0302390</b>                                  | B-73-A   | CP Handicap Handle Assembly (ADA Compliant)                                      |
| 10.                                                  | <b>0301082</b>                                  | A-6      | CP Handle Coupling                                                               |
| 11.                                                  | <b>0302109</b>                                  | B-7-A    | CP Socket Assembly                                                               |
| 12.                                                  | <b>5302274</b>                                  | B-32     | CP Handle Grip — 12 per package                                                  |
|                                                      | <b>0302389</b>                                  | B-74-A   | CP Handicap Handle Grip (ADA Compliant)                                          |

## TAILPIECES, CONTROL STOPS AND FLUSH CONNECTIONS

For additional information on tailpieces, control stops and flush connections see Showerheads, Parts and Accessories Tab.

| Item No. | Code No.                                            | Part No.  | Description                                             |
|----------|-----------------------------------------------------|-----------|---------------------------------------------------------|
| 13.      | <b>5302305</b>                                      | B-50-A    | Handle Repair Kit — 6 per package                       |
| 14.      | <b>5301139</b>                                      | A-31      | Handle Gasket — 48 per package                          |
| 15.      | <b>0306102</b>                                      | F-54-A    | 3/4" CP Spud Coupling Assembly                          |
|          | <b>0306142</b>                                      | F-55-A    | 1-1/4" CP Spud Coupling Assembly                        |
|          | <b>0306145</b>                                      | F-56-A    | 1-1/2" CP Spud Coupling Assembly                        |
| 15A.     | <b>SEE SLIP JOINT GASKETS AND RINGS TABLE BELOW</b> |           |                                                         |
| 16.      | <b>3323192</b>                                      | V-551-A   | Vacuum Breaker Repair Kit                               |
| 17.      | <b>5323005</b>                                      | V-500-AA  | 3/4" x 9" CP Vacuum Breaker — 6 per package             |
|          | <b>5323006</b>                                      | V-500-AA  | 1-1/4" x 9" CP Vacuum Breaker — 6 per package           |
|          | <b>5323007</b>                                      | V-500-AA  | 1-1/2" x 9" CP Vacuum Breaker — 6 per package           |
| 18.      | <b>0308676</b>                                      | H-550     | CP Stop Coupling†                                       |
| 19.      | <b>0308801</b>                                      | H-551-A   | CP Adjustable Tailpiece 2-1/16" long†                   |
| 20A.     | <b>5308696</b>                                      | H-553     | O-ring — 24 per package                                 |
| 20B.     | <b>5308381</b>                                      | H-552     | Locking ring — 12 per package                           |
| 21.      | <b>0388065</b>                                      | H-790-A   | 1" Screwdriver Bak-Chek® Stop CP — complete             |
|          | <b>0388064</b>                                      | H-790-A   | 3/4" Screwdriver Bak-Chek® Stop CP — complete           |
|          | <b>0388029</b>                                      | H-740-A   | 1" Screwdriver Bak-Chek® Stop CP — <b>OBSELETE</b>      |
|          | <b>0388031</b>                                      | H-740-A   | 3/4" Screwdriver Bak-Chek® Stop CP — <b>OBSELETE</b>    |
| 22.      | <b>3308853</b>                                      | H-541-ASD | 1" Control Stop Repair Kit *                            |
|          | <b>3308856</b>                                      | H-543-ASD | 3/4" Control Stop Repair Kit **                         |
| 23.      | <b>0308612</b>                                      | H-622     | CP Bonnet (Current Regal)                               |
|          | <b>0308991</b>                                      | H-639     | CP Bonnet — Pre 2010 Regal Stops*                       |
|          | <b>0308601</b>                                      | H-538     | CP Bonnet ** — <b>OBSELETE</b>                          |
| 24.      | <b>5388001</b>                                      | H-1012-A  | CP Cap — 6 per package VP                               |
| 25.      | <b>5310034</b>                                      | J-2/J-7   | Bumper Assembly — 6 per package — <b>OBSELETE</b>       |
| 26.      | <b>3308866</b>                                      | H-574     | Stop Cap, chrome plated with Seat Bumper (-YO)          |
| 27.      | <b>3308867</b>                                      | H-576     | Stop Cap, chrome plated with Extended Seat Bumper (-YG) |
| 28.      | <b>5388002</b>                                      | H-528     | Hole Plug                                               |
| 29.      | <b>3388015</b>                                      | H-1015    | Flow Control Kit (HEU Only) (not Shown)                 |

† See pages 100-101 for additional lengths

\*For use with 1" and 3/4" H-740-A CP (less cap) and 1" — H-540-A CP (with H-37 cap) Bak-Chek® screwdriver control stops


\*\*For use with 3/4" H-740-A CP Bak-Chek® screwdriver control stops

## ITEM 15A. SLIP JOINT GASKETS AND RINGS

| Size            | Code No.               | Part No. | Description                    |
|-----------------|------------------------|----------|--------------------------------|
| 1-1/2"          | <b>5306058</b>         | F-3      | Red Friction Ring              |
|                 | <b>5322001</b>         | VB-F-5   | Black Slip Joint Gasket        |
|                 | <b>0319086/5319086</b> | S-30     | Flexible Seat                  |
|                 | <b>0319079</b>         | S-21     | Rigid Seat (rubber over brass) |
| 1-1/2" x 1-1/4" | <b>0396062</b>         | F-105    | Slip Joint Gasket — Rigid      |
| 1-1/4"          | <b>5306057</b>         | F-3      | Red Friction Ring              |
|                 | <b>5322176</b>         | VB-F-5   | Black Slip Joint Gasket        |
|                 | <b>0307052/5307052</b> | G-21     | Rigid Seat (rubber over brass) |
| 1"              | <b>5306056</b>         | F-3      | Red Friction Ring              |
|                 | <b>5306115</b>         | F-5      | Black Slip Joint Gasket        |
| 3/4"            | <b>5306055</b>         | F-3      | Red Friction Ring              |
|                 | <b>5306113</b>         | F-5      | Black Slip Joint Gasket        |

## Regal® Flushometer

NOTE: Also for use with Regal® XL  
(Since mid-2010)



### MASTER FLUSHOMETER REBUILDING KITS (SEE PARTS LIST – ON PREVIOUS PAGE)

Refer to Parts List. Includes Items 7, 13, 16 & 20

| Code No.       | Part No. | Description                                        |
|----------------|----------|----------------------------------------------------|
| <b>3317001</b> | R-1001-A | Rebuild Kit (4.5 gpf/17.0 Lpf) Closet/Service Sink |
| <b>3317002</b> | R-1002-A | Rebuild Kit (1.5 gpf/5.7 Lpf) Urinal               |
| <b>3317003</b> | R-1003-A | Rebuild Kit (3.5 gpf/13.2 Lpf) Closet              |
| <b>3317004</b> | R-1004-A | Rebuild Kit (1.6 gpf/6.0 Lpf) Closet               |
| <b>3317005</b> | R-1005-A | Rebuild Kit (1.0 gpf/3.8 Lpf) LC Urinal            |
| <b>3317011</b> | R-1011-A | Rebuild Kit (0.5 gpf/1.9 Lpf) Urinal               |
| <b>3317012</b> | R-1012-A | Rebuild Kit (2.4 gpf/9.0 Lpf) Closet               |

### REPAIR KIT WASHER SET (SEE PARTS LIST – ON PREVIOUS PAGE)


|                |          |                                                |
|----------------|----------|------------------------------------------------|
| <b>5301189</b> | A-156-AA | Repair Kit Washer Set – Includes: 4, 5, 8 & 14 |
|----------------|----------|------------------------------------------------|

### ITEM 7. INSIDE PARTS KITS (SEE ILLUSTRATIONS BELOW)

| Item No. | Code No.       | Part No. | Application               |
|----------|----------------|----------|---------------------------|
| A.       | <b>3301036</b> | A-36-A   | 4.5 gpf/17.0 Lpf - Closet |
| B.       | <b>3301037</b> | A-37-A   | 1.5 gpf/5.7 Lpf - Urinal  |
| C.       | <b>3301038</b> | A-38-A   | 3.5 gpf/13.2 Lpf - Closet |
| D.       | <b>3301041</b> | A-41-A   | 1.6 gpf/6.0 Lpf - Closet  |
| E.       | <b>3301044</b> | A-42-A   | 1.0 gpf/3.8 Lpf - Urinal  |
| F.       | <b>3301081</b> | A-43-A   | 0.5 gpf/1.9 Lpf - Urinal  |
| G.       | <b>3301024</b> | A-44-A   | 2.4 gpf/9.0 Lpf - Closet  |
| H.       | <b>3301045</b> | A-140-A  | 1.28 gpf/4.8 Lpf - Closet |

### ITEM 7. INSIDE PARTS COMPONENTS (SEE ILLUSTRATIONS BELOW)

| Item No. | Code No.       | Part No. | Description                                                                      |
|----------|----------------|----------|----------------------------------------------------------------------------------|
| 3A.      | <b>5301058</b> | A-19-AC  | Relief Valve, White (Closet) – 12 per pkg.                                       |
| 3B.      | <b>5301059</b> | A-19-AU  | Relief Valve, Black (Urinal) – 12 per pkg.                                       |
| 3C.      | <b>5301211</b> | A-19-ALC | Relief Valve, Green (Closet/Urinal-LC) – 12 per pkg.                             |
| 3D.      | <b>0301143</b> | A-19-AL  | Relief Valve, Blue (9 Liter Closet)                                              |
| 4.       | <b>5301111</b> | A-15-A   | Disc – for all Inside Parts Kits – 12 per pkg.                                   |
| 5.       | <b>5301188</b> | A-156-A  | Diaphragm – for all Inside Parts Kits – 12 per pkg.                              |
| 6A.      | <b>5301236</b> | A-163-A  | Guide Assembly 4.5 gpf/17.0 Lpf Closet & 1.5 gpf/5.7 Lpf Urinal – 12 per package |
| 6B.      | <b>5301032</b> | A-152-A  | Guide Assembly 3.5 gpf/13.2 Lpf Closet – 12 per package                          |
| 6C.      | <b>5301031</b> | A-151-A  | Guide Assembly 1.6 gpf/6.0 Lpf LC Closet – 12 per package                        |
| 6D.      | <b>5301155</b> | A-155-A  | Guide Assembly 1.0 gpf/3.8 Lpf LC Urinal – 12 per package                        |
| 6E.      | <b>5301157</b> | A-157-A  | Guide Assembly 0.5 gpf/1.9 Lpf Urinal – 12 per package                           |



## Regal® Flushometer

NOTE: Also for use with Regal® XL  
(Since mid-2010)

### TROUBLESHOOTING GUIDE

**ATTENTION INSTALLERS:** With the exception of the control stop inlet, DO NOT USE pipe sealant or plumbing grease on any valve component or coupling! To protect the chrome or special finish of Sloan flushometers, DO NOT USE toothed tools to install or service these valves. Use our A-50 Super-Wrench™ or other smooth-jawed wrench to secure couplings. Regulations for low consumption fixtures (1.6 gpf/6.0 Lpf closets and 1.0 gpf/3.8 Lpf urinals) prohibit use of higher flush volumes.

#### 1. Flushometer DOES NOT function (no flush).

- A. Control stop or main valve is closed. Open control stop or main valve.
- B. Handle assembly is worn. Install handle repair kit B-50-A or replace handle.
- C. Relief valve is worn. Replace inside parts kit.

#### 2. Insufficient volume of water to adequately siphon fixture.

- A. Control stop not open enough. Adjust control stop for desired delivery of water.
- B. Urinal flushometer parts inside a closet flushometer. Replace inside urinal parts with proper closet flushometer parts.
- C. Low consumption flushometer installed on a non-low consumption fixture. Replace A-41-A inside parts kit with A-38-A water saver kit.
- D. Water saver kit installed in old, non-water saver bowl. Position refill head A-170-1 so that SIDE 1 is in the UP position.
- E. Inadequate volume or pressure at supply. If no gauges are available to properly measure supply pressure or volume of water at the flushometer, then remove the relief valve from the inside parts kit, reassemble the flushometer and open the control stop.
  - If the fixture siphons, more water volume is required. If a 3.5 gpf inside parts kit is installed in the flushometer, then first flip the refill head (under the diaphragm) to obtain a 4.5 gpf volume. If this volume is still inadequate, remove the flow ring from the guide to obtain a 6.5 gpf kit. If additional flow is still required, try a low pressure guide kit A-175-A. **IMPORTANT: LAWS AND REGULATIONS PROHIBIT THE USE OF HIGHER FLUSHING VOLUMES THAN LISTED ON FIXTURE OR FLUSHOMETER.**
  - If fixture does not siphon or if a low consumption fixture is installed, or if the above steps do not prove satisfactory, steps must be taken to increase the pressure and/or supply.

#### 3. Flushometer closes off immediately.

- A. Ruptured or damaged diaphragm. Install inside parts kit to correct above problems and update flushometer.
- B. Enlarged by-pass orifice from corrosion or damage. Install inside parts kit to correct above problem and update flushometer.

#### 4. Length of flush is too short (short flushing).

- A. Diaphragm assembly and guide assembly are not hand-tight. Screw the two assemblies hand-tight.
- B. Enlarged by-pass orifice from corrosion or damage. Install NEW inside parts kit to correct problem and update flushometer.
- C. A-19-AU (black) urinal relief valve in closet flushometer. Replace relief valve with A-19-AC (white) closet relief valve.
- D. B-41-A low consumption kit installed in non-low consumption fixture. Replace with proper inside parts kit.
- E. Handle assembly is worn. Install handle repair kit B-50-A or replace the handle.

#### 5. Length of flush is too long (long flushing) or fails to close off.

- A. Relief valve is not seating properly or by-pass orifice is clogged because of foreign material, or by-pass orifice is closed by an invisible gelatinous film from "over-treated" water. Disassemble the working parts and wash thoroughly.  
NOTE: SIZE OF ORIFICE IN THE BY-PASS IS EXTREMELY IMPORTANT FOR PROPER METERING OF WATER INTO THE UPPER CHAMBER OF THE FLUSHOMETER. DO NOT ENLARGE OR DAMAGE THIS ORIFICE. REPLACE INSIDE KIT IF CLEANING DOES NOT CORRECT PROBLEM.
- B. Line pressure has dropped and is not sufficient to force relief valve to seat. Shut off all control stops until pressure has been restored, then open them again.
- C. A-19-AC (white) closet relief valve has been used in a 1 or 1-1/2 gpf urinal. Replace with A-19-AU (black) relief valve.
- D. Inside cover is cracked or damaged. Replace the inside cover A-71.

#### 6. Chattering noise in flushometer.

- A. The A-156-A segment diaphragm has been installed upside-down. Replace the segment diaphragm to the proper position as instructed by markings on the diaphragm.
- B. The inside cover has been distorted from wear, freezing or abuse. replace inside cover.

#### 7. Leaking at handle assembly.

- A. The B-39 seal is worn or deteriorated. Install new B-39 seal.  
NOTE: The B-39 seal will easily slide right onto the B-40 bushing if it is wet.
- B. Handle gasket has been omitted. Install A-31 handle gasket or handle repair kit B-50-A.
- C. Valve handle bushing is worn. Install handle repair kit B-50-A.

### CARE AND CLEANING INSTRUCTIONS

**DO NOT USE** abrasive or chemical cleaners (including chlorine bleach) to clean flushometers that may dull the luster and attack the chrome or special decorative finishes. Use **ONLY** mild soap and water, then wipe dry with a clean towel or cloth.

While cleaning the bathroom tile, protect the flushometer from any splattering of cleaner. Acids and cleaning fluids will discolor or remove chrome plating.

**When assistance is required, please contact  
Sloan Technical Support at: 1-888-SLOAN-14 (1-888-756-2614).**